



About	Exhibits	Updates	Equipment
Supporters			
Docs / info		Wanted!	Sales
Links / traders			

Telefunken RS337 pentode



The valve measures 200x55mm overall and has a 5-pin base.

Markings on the glass are:

Telefunken
 RS337
 Nr. 507995/0541/IV
 12,0V

Eigentum
 R.L.

Filament voltage	12V
Filament current	2.75A
Max anode voltage	1500V
Mutual conductance	2.8mA/V max
Max anode dissipation	110W
Max screen dissipation	25W



